

TECHSPEC® 25mm Diameter x 75mm FL Uncoated, UV PCX Cylinder Lens



Stock #68-173 CLEARANCE 3-5 DAYS

- 1 + **S\$159.43**

ADD TO CART

Qty 1+

S\$159.43

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
25.00 +0.0/-0.2

Effective Focal Length EFL (mm):
75.00

Substrate: ☐
[Fused Silica](#) (Coming 7980)

f/#:
3.00

Numerical Aperture NA:
0.17

Coating: Uncoated
Type: Cylinder Lens, Plano-Convex
Wavelength Range (nm): 200 - 2200
Back Focal Length BFL (mm): 72.60
Center Thickness CT (mm): 3.50
Center Thickness Tolerance (mm): ±0.1
Edge Thickness ET (mm): 1.15
Focal Length Tolerance (%): ±3
Radius R (mm): 34.39
Surface Quality: 40-20
Wedge Tolerance (arcmin): 15.00

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View