

2.5mm FL, High Resolution, f/2, Micro Video Lens



Stock **#34-711** 3-5 DAYS

-

1

+

S\$107.30

ADD TO CART

Qty 1-49
S\$107.30
Qty 50+
S\$82.65
Volume Pricing
Request Quote

Get Product Downloads

Length (mm):
17.97

Maximum Diameter (mm):
20

Maximum Image Circle (mm):
6.50

Horizontal Field of View @ Max Sensor Format:
125

Resolution, On-Axis: 100 lp/mm @64% Contrast
Resolution, 0.7 Field: 100 lp/mm @57% Contrast
Resolution, Full Field: 100 lp/mm @34% Contrast
Note: High Resolution
TV Distortion (%): -36
Type: M12 Imaging Lens
Focal Length FL (mm): 2.50
Maximum Sensor Format: 1/2.8"
Working Distance (mm): 400 - ∞
Mount: M12 x0.5 (S-Mbunt)
Aperture (f/#): f/2
IR Cut Filter: No
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Contains SVHC(s)
Certificate of Conformance: View