

2.5mm FL, No IR-Cut Filter, f/2.5, Micro Video Lens



Stock #57-681 3-5 DAYS

− 1 +

S\$87.00

ADD TO CART

Qty 1-49

S\$87.00

Qty 50+

S\$68.15

Volume Pricing

[Request Quote](#)

Get Product Downloads

Length (mm):
19.10

Filter Thread:
M12 x 0.50

Maximum Diameter (mm):
17.0

Maximum Image Circle (mm):
6.00

Horizontal Field of View @ Max Sensor Format: 115.8
Resolution, On-Axis: 63 lp/mm @ 20% Contrast
Resolution, 0.7 Field: 48 lp/mm @ 20% Contrast
Resolution, Full Field: 30 lp/mm @ 20% Contrast
Note: Standard
Type: M12 Imaging Lens
Focal Length FL (mm): 2.50
Maximum Sensor Format: 1/3"
Working Distance (mm): 400 - ∞
Mount: M12 x 0.5 (S-Mbunt)
Aperture (f/#): f/2.5
Distortion (%): -60 @ Full Field
IR Cut Filter: No
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Contains SVHC(s)
Certificate of Conformance: View