

**TECHSPEC® 25mm ID Fixed Angle Mounting Plate**



#85-617

Stock **#85-617** **5 In Stock**

- 1 + **\$64<sup>05</sup>**

**ADD TO CART**

Volume Pricing

Qty 1+	<b>\$64.05</b> each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Function:  
Angle Adjustment

**Physical & Mechanical Properties**

Plate Inner Diameter (mm):  
25.0

Bolt Circle Diameter for M3 C'bore (mm):  
38.0

Construction:  
Black Anodized Aluminum

50 Dia. **Dimensions (mm):**

10.00 **Thickness (mm):**

## Regulatory Compliance

**Compliant** **RoHS 2015:**

**View** **Certificate of Conformance:**

**Compliant** **REACH 241:**

## Product Details

- Multiple Angular Positioning Options
- Fixed and Continuous Adjustment Plates Available
- Anodized Aluminum Construction

TECHSPEC® Cage System Angle Adjustment Plates attach to [standard mounting plates](#) via angle brackets, and offer a range of angular positioning options. The fixed angle mounting plates feature M3 C-Bore holes positioned at 30° increments to introduce 30°, 60°, or 90° bends in the optical path. Swivel adapter plates are designed to be used in pairs, and enable continuous angle adjustment. [#85-692](#) or [#85-701](#) post adapter for 25mm plates serves as a joint between two swivel adapter plates. Suspending a tilt plate between two standard cage system plates allows an optic or mount to be tilted with respect to the optical axis.

### Quick Video Demonstration

Maximize your application performance with the right products. View a quick video demonstration of TECHSPEC Cage System components: [How to Build a Swivel Joint Assembly](#).