

**TECHSPEC® 25mm Length, C-Mount Extension Tube**



Stock #58-736 **20+ In Stock**

- 1 + \$61.00

**ADD TO CART**

Volume Pricing	
Qty 1-4	\$61.60 each
Qty 5-9	\$55.02 each
Qty 10-25	\$51.10 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Extension Tube **Type:**  
Extension Tube (Fixed) **Function:**

**Physical & Mechanical Properties**

25.0 **Extension Length (mm):**

29.0 **Total Length (mm):**

22.0 **Clear Aperture CA (mm):**

30.0 **Outer Diameter (mm):**

## Threading & Mounting

C-Mount **Thread Type:**

## Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Compliant](#) **REACH 241:**

## Product Details

- Used for Adding a Fixed Tube Extension to Optical Systems
- Feature Male/Female Threads at Opposite Ends
- Black Anodized Aluminum Construction

TECHSPEC® C, S, and T-Mount Extension Tubes add extension length to an optical system while blocking external light and debris from entering the system. Extension tubes are available with C, S, or T-Mount threading, allowing them to be integrated into a wide range of systems and applications. Their black anodized aluminum construction, combined with a threaded inner diameter, ensures that stray light is reduced within the system. TECHSPEC C, S, and T-Mount Extension Tubes feature different lengths that can be combined to create the exact extension length needed for a specific application. The actual tube length is longer than the extension length due to the male threaded portion.

## Technical Information

