

## 25mm MegaPixel Fixed Focal Length Lens



MegaPixel Fixed Focal Length Lenses

Stock **#56-789** **6 In Stock**

[Similar Products](#)

-

1

+

S\$465<sup>00</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1+         | S\$465.00 each                |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

General

|                                     |                 |
|-------------------------------------|-----------------|
|                                     | Product Family: |
| MegaPixel Fixed Focal Length Lenses |                 |
|                                     | Type:           |
| Fixed Focal Length Lens             |                 |

Physical & Mechanical Properties

|          |              |
|----------|--------------|
|          | Iris Option: |
| Variable |              |
|          | Length (mm): |
| 36.00    |              |

|       |                               |
|-------|-------------------------------|
| 33.50 | Maximum Diameter (mm):        |
| 33.5  | Outer Diameter (mm):          |
| 71.00 | Weight (g):                   |
| 1.10  | Maximum Rear Protrusion (mm): |

|                    |                                            |
|--------------------|--------------------------------------------|
| Optical Properties |                                            |
| 77.00              | Field of View @ Min Working Distance (mm): |
| 14.60°             | Horizontal Field of View, 1/2" Sensor:     |
| 11.00              | Maximum Image Circle (mm):                 |
| 25.00              | Focal Length FL (mm):                      |
| 300 - ∞            | Working Distance (mm):                     |
| f/1.4 - f/16       | Aperture (f/#):                            |
| -0.3               | Maximum Distortion (%):                    |
| VIS                | Lens Wavelength Range:                     |

|        |                        |
|--------|------------------------|
| Sensor |                        |
| 2/3"   | Maximum Sensor Format: |
| 6.20   | Pixel Size (µm):       |

|                      |                |
|----------------------|----------------|
| Threading & Mounting |                |
| M30.5 x 0.50         | Filter Thread: |
| C-Mount              | Mount:         |

|                       |                             |
|-----------------------|-----------------------------|
| Regulatory Compliance |                             |
| Exempt                | RoHS 2015:                  |
| Contains SVHC(s)      | Reach 224:                  |
| View                  | Certificate of Conformance: |

## Product Details

- Up to 2/3", C-Mount Lens
- Ideal for Machine Vision at an Economical Price
- 5mm to 75mm Focal Length

MegaPixel Fixed Focal Length Lenses are designed for high-resolution imaging. The lenses are ideal for machine vision applications with demanding space constraints. These lenses complement the resolution of many MegaPixel cameras with 1/2" or 2/3" formats. Low distortion and high resolution enable these economically priced lenses to produce sharp, high-contrast images compared to standard CCTV and compact lenses. MegaPixel Fixed Focal Length Lenses are available in focal lengths ranging from 5 to 75mm. Locking screws for the manual iris and focus allow these lenses to be used in high-vibration environments. Typical applications include [factory automation](#), inspection, and macro work.

**Note:** For [#64-869](#) 75mm FL Lens, remove focus limit screw to focus past 1.2m.

## Technical Information

### #56-789 25mm Megapixel Fixed Focal Length Lens



