

25mm sq - Rectangular Bar Clamp



Stock **#54-994** **6 In Stock**

-

1

+

S\$150^{.84}

ADD TO CART

Volume Pricing	
Qty 1-9	S\$150.84 each
Qty 10-25	S\$135.76 each
Qty 26-49	S\$128.44 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

- Type:
- Fixed
- Type of Optics:
- Square or Rectangular

Physical & Mechanical Properties

Construction:

Black Anodized Aluminum, Stainless Steel Post

Edge Thickness of Compatible Optics (mm):

8.5 (Max)

Threading & Mounting

Size of Compatible Optics (mm):

5.0 - 25.0

Compatible Post:

M6 x 1.0

Regulatory Compliance

RoHS 2015:

Exempt

Certificate of Conformance:

View

Reach 247:

Contains SVHC(s)

PRODUCT DETAILS

- Black Anodized Aluminum
- M6 x 1.0 Mounting Thread
- **Posts** and **Post Holders** Required for Mounting

Metric Rectangular Optic Mounts have a bar-type design with non-marring mounting surfaces, making it ideal for rectangular optics such as filters and mirrors, as well as cylindrical lenses. The mounts are available in 25 or 60mm sq for rectangular or square optics. They are compatible with a M6 x 1.0 mounting thread. Metric Rectangular Optic Mounts are constructed of black anodized aluminum with a stainless-steel post. [Posts](#) and [Post Holders](#) are required for mounting to a breadboard.

TECHNICAL INFORMATION

A	B	C	D	E	F	G	H	Stock No.
30	25	40	48	12	10	1.0	8.5	#54-994
60	60	85	95	14	15	1.5	12	#54-995

Optic Clamp Screw

Units: mm