

25mm Travel, 0.01mm Grad. Mic. Drive S-Face



Drive Mechanisms

Stock #33-731 **4 In Stock**

⊖ 1 ⊕ S\$142⁰⁰

ADD TO CART

Volume Pricing

Qty 1-9	S\$142.80 each
Qty 10-24	S\$128.52 each
Need More?	Request Quote

Product Downloads

General

Metric **Type:**

Mitutoyo **Manufacturer:**

w/ Ratchet **Note:**

Physical & Mechanical Properties

Travel (mm):

25

Graduation (mm):

0.01

Stem Diameter (mm):

10

Stem/Spindle:

Plain/Spherical

Stem Length (mm):

15

Spindle Diameter (mm):

6.35

Min. Spindle Length (mm):

27

Max. Diameter (mm):

18

Overall Length (mm):

109

Hardware & Interface Connectivity

Type of Drive:

Metric Micrometer

Regulatory Compliance

RoHS 2015:

[Exempt](#)

Certificate of Conformance:

[View](#)

REACH 241:

[Contains SVHC\(s\)](#)

Product Details

- Micrometer, Fine Screw, Digital and Differential Options Available
- Compatible with our [Ball Bearing Stages](#)

These drive mechanisms add versatility to our selection of [ball bearing stages](#). Four options are available: micrometer (English and Metric), fine screw, digital, and differential.

Please reference individual product descriptions to see which stages are compatible with each drive mechanism.

;