

TECHSPEC®

25mm Uncoated Dove Prism



Stock **#45-403** 3-5 DAYS

-

1

+

S\$276.95

ADD TO CART

Qty 1-5

S\$276.95

Qty 6+

S\$249.25

Volume Pricing

[Request Quote](#)

Get Product Downloads



Coating:

Uncoated

Substrate:

[N-BK7](#)

Height (mm):

25.0

Length (mm):

103.18
Surface Quality: 60-40
Type: Dove Prism
Dimensional Tolerance (mm): ±0.13 Legs, ±0.25 Length
Angle Tolerance (arcmin): 2.00
Bevel: Protective bevel as needed
Image Orientation: Left-Handed
Ray Deviation (°): 0
Surface Flatness (P-V): λ/8 (Entrance and Exit Faces)

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View