

25mm x 25mm Mounting Stage Size, Metric Z-Axis Stage



Stock **#56-334** [CONTACT US](#)

-

1

+

S\$821^{.43}

ADD TO CART

Volume Pricing	
Qty 1-4	S\$821.43 each
Qty 5+	S\$726.00 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

Type:

Metric

Physical & Mechanical Properties

Type of Movement:

Linear (Z)	
Slide-Fit	Guide System:
25 x25	Stage Size (mm):
None	Center Hole:
Aluminium Stage	Construction:
±2.5	Height Adjustment (mm):
1	Load Capacity (kg):
(3) 2.5mm Diameters on 20mm Sq.	S.H.C.S. C'bore:
3	Straight Line Accuracy (µm):
0.5	Travel Per Knob Rotation (mm):
0.07	Weight (kg):

Hardware & Interface Connectivity

Metric Micrometer	Type of Drive:
-------------------	----------------

Threading & Mounting

(7) M2 x0.4	Mounting Threads:
-------------	-------------------

Regulatory Compliance

Exempt	RoHS 2015:
View	Certificate of Conformance:
Contains SVHC(s)	Reach 247:

PRODUCT DETAILS



- Fine Micrometer Movement
- Available in Four Sizes
- Black Anodized Aluminum
- Locking Knob

Metric Z-Axis Stages provides micrometer movement for optical components. One rotation of the knob equals 0.5mm. Height adjustment is ±2.5mm for 25mm and 40mm stages and ±5.0mm for 60mm and 80mm stages. Metric Z-Axis Stages are available are constructed of black anodized aluminum and feature a locking knob. The stages are available in four sizes.

40mm square, 8mm thick top mounting adapter plate [#58-290](#) mounts to M3 holes and provides a counterbore for 1/4-20 or M6 socket head cap screw. Compatible with the following stages: [#55-029](#), [#55-030](#), [#55-031](#), [#55-838](#), and [#55-839](#).

60mm square Z-Axis Stage (#55-032) and 80mm square Z-Axis Stage (#56-335) are compatible with the following stages: [#54-687](#), [#55-459](#), [#55-840](#), [#55-841](#), and [#56-335](#).

TECHNICAL INFORMATION



#56-334

Units: mm