

## 25X Peak Direct Measuring Microscope



Peak Direct Measuring Microscopes

Stock **#39-110** **4 In Stock**

⊖ 1 ⊕ **S\$449<sup>00</sup>**

**ADD TO CART**

### Volume Pricing

Qty 1-4	<b>S\$449.40</b> each
Qty 5+	<b>S\$426.30</b> each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### Physical & Mechanical Properties

3.30 **Field of View (mm):**

At Focus: 41.5 Dia. x 122 L **Dimensions (mm):**

0.05 **Graduation (mm):**

0 - 3.0 **Reticle Scale (mm):**

Up to 22 **Depth Measurements (mm):**

## Optical Properties

25X **Magnification:**

17.0 **Working Distance (mm):**

## Regulatory Compliance

[View](#) **Certificate of Conformance:**

## Product Details

Reticle should not be removed or replaced.

- Multiple Magnification Options
- Illuminated Models Available with English or Metric Reticles
- Removable Clear Acrylic Base

Peak Direct Measuring Microscopes are high power, portable microscopes designed for precise depth measurements. Peak Direct Measuring Microscopes feature a 10X focusable eyepiece and a scale with an accuracy of 0.1mm for measuring the length, width, or depth of an object. The clear cutaway acrylic base allows for manipulation of the sample while viewing. Illuminated models feature a removable pen illuminator, and include two AA batteries. Peak Direct Measuring Microscopes are sold with a hard-shell vinyl storage case.

**Note:** Reticle should not be removed or replaced.