

## 2.62", English Rotary Stage



Stock #38-193 CLEARANCE 2 In Stock

S\$1,652<sup>00</sup>

ADD TO CART

### Volume Pricing

|            |                               |
|------------|-------------------------------|
| Qty 1+     | S\$1,652.00 each              |
| Need More? | <a href="#">Request Quote</a> |

### Product Downloads

### General

English Type:

### Physical & Mechanical Properties

Rotary Type of Movement:

Ball Bearing Guide System:

66.5 x 66.5 Stage Size (mm):

Travel (°):

±5 (Fine), 360 (Coarse)

Center Hole:  
0.50" Dia. Thru

Construction:  
Aluminum top and base; steel tangent arm drive

Increments (arcmin):  
12

Load Capacity, Normal (lbs):  
10

Load Capacity, Vertical (lbs):  
4

Stage Size (inches):  
2.62 x 2.62

Weight (lbs):  
1.8

Table Diameter (inches):  
2.62

## Hardware & Interface Connectivity

Type of Drive:  
Tangent Arm

## Threading & Mounting

Mounting Threads:  
(4) 6-32 on 1.125" dia. B.C., (4) 1/4-20 on 2.00" dia. B.C.

## Regulatory Compliance

RoHS 2015:  
[Compliant](#)

Certificate of Conformance:  
[View](#)

## Product Details

- Low Wear, Low Friction Movement with Coarse or Fine Adjustment
- 2 or 2.62" Diameter Stages with Tapped Mounting Holes
- Calibrated Dial with 12 Minute Vernier for Accurate Read-Out

Compact miniature stages provide low-friction rotary movement with both coarse and fine adjustment. This allows for quick rotation over a continuous 360° travel, plus precise angular adjustment at any selected position. Features include preloaded angular contact ball bearing system, a positive position lock, a 2.00" or 2.62" diameter stage with tapped mounting holes and a calibrated dial with six minute vernier for accurate positional read-out. It can be combined with our compatible linear translation stages for multi-axis linear-rotary applications.

## Technical Information

