

26mm Diameter, 4-6λ Mirror



4-6λ First Surface Mirrors

Stock **#31-009** 3-5 DAYS



1



S\$28.27

ADD TO CART

Qty 1-5

S\$28.27

Qty 6+

S\$22.47

Volume Pricing

[Request Quote](#)

Get Product Downloads

Diameter (mm):
26.00 ±0.76

Surface Flatness (P-V):
4 - 6λ

Substrate: ☐
Float Glass

Surface Quality:

80-50
Coating Specification: R _{avg} >85% @400 - 700nm
Coating: Protected Aluminum (400-700nm)
Coating Type: Metal
Angle of Incidence (°): 45.00
Bevel: Protective as needed
Clear Aperture (%): >90
Thickness (mm): 3.00 nominal
Type: Flat Mirror
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant