

2° Commercial Grade Wedge Prism



Stock #27-677

CLEARANCE

3-5 DAYS

-

1

+

S\$36.18

ADD TO CART

Qty 1+

S\$36.18

Volume Pricing

[Request Quote](#)

Get Product Downloads

Coating:

MgF₂ (400-700nm)

Angle Tolerance (arcmin):

1.00

Coating Specification:

R_{avg} ≤1.75% @ 400 - 700nm

Diameter (mm):

25.00 ±0.1

Image Orientation:

Beam Deviation

Power (diopters): 3.49
Substrate: □ N-BK7
Surface Accuracy: 1λ
Thickness (mm): 3.00
Type: Wedge Prism
Wedge Angle: 3° 52'0"
Wedge Angle Deviation (°): 2.00

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View