

3" Diameter Rotary Plate



Stock **#56-664** 20+ In Stock

-

1

+

S\$139^{.64}

ADD TO CART

Volume Pricing	
Qty 1-9	S\$139.64 each
Qty 10+	S\$123.96 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General	
English	Type:
Rotation	Function:

Physical & Mechanical Properties	
12.70	Thickness (mm):
Construction: Black Anodized Aluminum and Stainless Steel	
76.2	Outer Diameter (mm):
Threading & Mounting	
Mounting Threads: (8) 1/4-20 Female, (1) 1/4-20 Male	
Regulatory Compliance	
Compliant	RoHS 2015:
Compliant	Reach 224:
View	Certificate of Conformance:

PRODUCT DETAILS

- Increase the Versatility of Existing Mounting Equipment
- Ideal for Direct Mounting to Standard Breadboards
- Aluminum Plate with 1/4-20 Counterbored Holes

This rotary base plate features slots on a 2" diameter bolt circle which allow adjustments to 70°. Also features a center pin for 360° rotation.

TECHNICAL INFORMATION

