

30° Full Fan Angle Laser Line Generator Lens



Powell Lenses

Stock #43-473 3-5 DAYS



1



S\$337.85

ADD TO CART

Qty 1-5

S\$337.85

Qty 6+

S\$270.43

Volume Pricing

[Request Quote](#)

Get Product Downloads

Diameter (mm):
8.90 +0.00/-0.15

Substrate:
[N-BK7](#)

Coating:
VIS-NIR (450-900nm)

Type:

Beam Shaping Lens
Wavelength Range (nm): 450 - 900
Coating Specification: BBAR @ 450 - 900nm
Height (mm): 8.90 +0.00/-2.00
Index of Refraction n_d: 1.517
Fan Angle (°): 30.00

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View