

[See all 64 Products in Family](#)

Coherent® StingRay™ Projection Head 1254118 | 514nm, 30° Fan

See More by [Coherent®](#)



30° Line, 514nm Stingray Projection Head, #89-574

Stock **#89-574** **1 In Stock**

⊖ 1 ⊕ **S\$487⁰⁰**

ADD TO CART

Volume Pricing	
Qty 1+	S\$487.00 each
Need More?	Request Quote

Product Downloads



General

1 Line **Type:**

Compatible Laser Models:
[86-848, 87-522](#)

Manufacturer:
Coherent®

Optical Properties

Wavelength (nm):
514.00

Green **Color:**

30.00 **Fan Angle (°):**

Regulatory Compliance

Compliant **RoHS 2015:**

View **Certificate of Conformance:**

Product Details

- External Focus with up to 100mW Output Power
- Auto Scaling Input Power 5 - 24VDC with Reverse Polarity Protection
- Built-In Microcontroller for Fault Monitor
- **Coherent® StingRay™ Developer's Kit** also available

Coherent® StingRay™ and BioRay™ Laser Diode Modules are ideal for a variety of alignment, machine vision, and biomedical applications. They are available in a wide range of output powers, wavelengths, and fan angles. High precision optical components and sophisticated drive electronics provide power and control to your application, reducing signal-to-noise ratios and increasing measurement speed. Coherent® StingRay™ and BioRay™ Laser Diode Modules are designed with a flat top power distribution across the beam profile for consistency in line projection widths.

Note: For CDRH certified systems (Class IIIb), **#86-878** Laser Controller and additional external voltage source (0.5□5V) with BNC connector is required.