

[See all 64 Products in Family](#)

Coherent® StingRay™ Projection Head 1277523 | 640nm, 5mW, 30° Fan

See More by [Coherent®](#)



Stock **#89-587** 1 In Stock

-

1

+

S\$491^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	S\$491.00 each
Need More?	Request Quote

Product Downloads

General	
Type:	1 Line, Extended Focus
Compatible Laser Models:	86-849
Manufacturer:	Coherent®
Optical Properties	

640.00	Wavelength (nm):
Red	Color:
30.00	Fan Angle (°):
Electrical	
5.00	Maximum Power (mW):
Regulatory Compliance	
Exempt	RoHS 2015:
Contains SVHC(s)	Reach 224:
View	Certificate of Conformance:

Product Details

- External Focus with up to 100mW Output Power
 - Auto Scaling Input Power 5 - 24VDC with Reverse Polarity Protection
 - Built-In Microcontroller for Fault Monitor
 - [Coherent® StingRay™ Developer's Kit](#) also available
- Coherent® StingRay™ and BioRay™ Laser Diode Modules are ideal for a variety of alignment, machine vision, and biomedical applications. They are available in a wide range of output powers, wavelengths, and fan angles. High precision optical components and sophisticated drive electronics provide power and control to your application, reducing signal-to-noise ratios and increasing measurement speed. Coherent® StingRay™ and BioRay™ Laser Diode Modules are designed with a flat top power distribution across the beam profile for consistency in line projection widths.
- Note:** For CDRH certified systems (Class IIIb), [#86-878](#) Laser Controller and additional external voltage source (0.5-5V) with BNC connector is required.