

# 300 x 300mm Right-Handed Plastic Circular Polarizer (CP42HER)



Stock #14-357 CLEARANCE 3-5 DAYS

-

1

+

**S\$283.43**

ADD TO CART

|           |
|-----------|
| Qty 1+    |
| S\$283.43 |

|                               |
|-------------------------------|
| Volume Pricing                |
| <a href="#">Request Quote</a> |

Get Product Downloads

Substrate: [Polymer Film CP42HER](#)

Length (mm):  
300.00

Operating Temperature (°C):  
-40 to +80

Dimensions (mm):  
300.0 x 300.0

Thickness (mm):  
0.27 ±0.04

|                                                 |
|-------------------------------------------------|
| <b>Thickness Tolerance (mm):</b><br>±0.03       |
| <b>Transmission (%):</b><br>42                  |
| <b>Type:</b><br>Right-Handed Circular Polarizer |
| <b>Dimensional Tolerance (mm):</b><br>+0.0/-3.0 |
| <b>Construction:</b><br>Polarizing Film         |
| <b>Wavelength Range (nm):</b><br>400 - 700      |
| <b>Polarization Efficiency (%):</b><br>>99.90   |
| <b>Width (mm):</b><br>300.00                    |
| <b>#Sorting:</b><br>33.00                       |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 235:</b><br><a href="#">Contains SVHC(s)</a>      |