

TECHSPEC® 30mm, 40mm Radius, English Goniometer



30mm, 40mm Radius, English Goniometer

Stock **#66-520** 3-5 DAYS

⊖ 1 ⊕ **\$S529.25**

ADD TO CART

Qty 1-2

\$S529.25

Qty 3+

\$S461.54

Volume Pricing

[Request Quote](#)

Get Product Downloads

Type of Movement:
Goniometer

Type of Drive:
Lead Screw

Type:
English

Stage Size (mm):

30 x 30
Travel (°): ±15
Construction: Brass Stage
Leadscrew Pitch (mm): 0.5
Load Capacity (kg): 2
Mounting Threads: (1) ¼-20, (8) 2-56
Radius R (mm): 40
Resolution (arcmin): 5
Stage Size (inches): 1.18 x 1.18
Weight (kg): 0.15

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant