

TECHSPEC® 30mm, 82mm Radius, Metric Goniometer



TECHSPEC® Goniometers



Stock **#66-525** 3-5 DAYS

- 1 + **S\$662.65**

ADD TO CART

Qty 1-2

S\$662.65

Qty 3+

S\$578.84

Volume Pricing

[Request Quote](#)

Get Product Downloads

Type of Movement:
Goniometer

Type of Drive:
Lead Screw

Type:

Metric
Stage Size (mm): 30 x 30
Travel (°): ±7.5
Construction: Brass Stage
Leadscrew Pitch (mm): 0.5
Load Capacity (kg): 2
Mounting Threads: (1) M6 x 1, (8) M2 x 0.4
Radius R (mm): 82
Resolution (arcmin): 10
Stage Size (inches): 1.18 x 1.18
Weight (kg): 0.15

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant