

30mm Dia. 405nm $\lambda/4$ Quartz Waveplate Multiple Order



Stock #83-925 CLEARANCE 3-5 DAYS

- 1 + **S\$366.78**

ADD TO CART

Qty 1+

S\$366.78

Volume Pricing

[Request Quote](#)

Get Product Downloads

Clear Aperture CA (mm):
23.0

Coating:
Laser V-Coat (405nm)

Design Wavelength DWL (nm):
405

Diameter (mm):
30.00 +0.00/-0.25

Substrate: ☐
Crystal Quartz

Retardance: λ/4
Surface Quality: 10-5
Thickness (mm): 6.00 +0.00/-0.25
Type: Crystalline Waveplate
Construction: Crystalline
Transmitted Wavefront, P-V: λ/8 for central 80% of clear aperture
Parallelism (arcsec): <3
Retardance Tolerance: ±λ/200
Temperature Coefficient (λ/°C): 0.0015
Retardance Order: Multiple Order

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View
