

TECHSPEC® 3.0mm Diameter x 10.0mm Length, N-BK7 Rod Lens



Stock **#45-940** 20+ In Stock

- 1 + S\$78⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-5	S\$78.40 each
Qty 6-25	S\$63.00 each
Qty 26-49	S\$58.80 each
Need More?	Request Quote

Product Downloads

General

Rod Lens **Type:**

Physical & Mechanical Properties

3.00 +0.00/-0.03 **Diameter (mm):**

10.00 **Length (mm):**

+0/-0.1 Length Tolerance (mm):

Optical Properties

N-BK7 Substrate:

Uncoated Coating:

350 - 2200 Wavelength Range (nm):

40-20 Surface Quality:

Regulatory Compliance

Compliant RoHS 2015:

Compliant Reach 224:

View Certificate of Conformance:

Product Details

- Focuses Collimated Light into a Line
 - Available in Diameters as Small as 1mm
- TECHSPEC® Rod Lenses are polished on the circumference and ground on both ends. Optical performance is similar to a cylinder lens. Collimated light passing through the diameter of the rod lens will be focused into a line. TECHSPEC® Rod Lenses are offered in diameters ranging from 1mm to 10mm.

Technical Information

Rod Lens

