

TECHSPEC[®] 30mm ID Side Access Mounting Plate, 60° Cutout



#85-717 + #85-641

Stock **#85-641** 1 In Stock

-

1

+

S\$134⁴⁰

ADD TO CART

Volume Pricing	
Qty 1+	S\$134.40 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

Black Anodized Aluminum	Note:
Fixed	Function:

Physical & Mechanical Properties

50 Dia.	Dimensions (mm):
---------	------------------

10.00	Thickness (mm):
30.0	Plate Inner Diameter (mm):
38.0	Bolt Circle Diameter for 6mm Dia. Thru (mm):
38.0	Bolt Circle Diameter for M3 C'bore (mm):
38.0	Bolt Circle Diameter for M3 Thru (mm):

Threading & Mounting

C'Bore Holes: (8) M3 Rod Thru Holes: (4) 6 60° cutout for side access	Mounting Threads:
---	-------------------

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 233:

PRODUCT DETAILS

• Specialized Plates Designed to Hold and Position Optics
• Filter Holder Plate with Interchangeable Filter Holder
These specialized TECHSPEC® Cage System Filter Holder Plates and Filter Holders are designed to hold and position a range of [optical components](#). Like a standard cage system plate, the anodized aluminum, U-shaped Filter Holder Plate features 6mm rod holes, in addition to being able to accept a Delrin® interchangeable filter holder that easily slides into the filter holder plate.

Quick Video Demonstration

Maximize your application performance with the right products. View a quick video demonstration of TECHSPEC Cage System components: [Filter Holder Plate and Interchangeable Filter Holder](#).