

[See all 7 Products in Family](#)

TECHSPEC<sup>®</sup>

30R/70T NIR, C-Mounted Plate Beamsplitter



Stock **#49-687**

CONTACT US

-

1

+

S\$467<sup>.60</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-4        | S\$467.60 each                |
| Qty 5-9        | S\$408.80 each                |
| Qty 10+        | S\$383.60 each                |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

| General                                                                        |               |
|--------------------------------------------------------------------------------|---------------|
| Standard Beamsplitter                                                          | Type:         |
| Beamsplitter Included:<br>Standard 30R/70T NIR Plate Beamsplitter, 1 $\lambda$ |               |
| Physical & Mechanical Properties                                               |               |
| Plate                                                                          | Construction: |

|                         |                             |
|-------------------------|-----------------------------|
| +0.0/-0.25              | Dimensional Tolerance (mm): |
| 38.0                    | Extension Length (mm):      |
| Black Anodized Aluminum | Housing:                    |

|              |                    |
|--------------|--------------------|
| 38 x 38 x 50 | Housing Dimension: |
|--------------|--------------------|

Optical Properties

|                                                                 |                                      |
|-----------------------------------------------------------------|--------------------------------------|
| Surface 2: Multi-Layer Anti-Reflection for Near-Infrared Region | Coating Specification:               |
| 30/70                                                           | Reflection/Transmission Ratio (R/T): |

|       |                                        |
|-------|----------------------------------------|
| ±5    | Reflection/Transmission Tolerance (%): |
| N-BK7 | Substrate: <input type="checkbox"/>    |

|       |                         |
|-------|-------------------------|
| 1λ    | Surface Flatness (P-V): |
| 60-40 | Surface Quality:        |

|            |                        |
|------------|------------------------|
| 700 - 1100 | Wavelength Range (nm): |
|------------|------------------------|

Threading & Mounting

|                       |              |
|-----------------------|--------------|
| C-Mount Enclosure     | Mount:       |
| C-Mount (1" x 32 TPI) | Thread Type: |

Regulatory Compliance

|                      |                             |
|----------------------|-----------------------------|
| <a href="#">View</a> | Certificate of Conformance: |
|----------------------|-----------------------------|

## Product Details

- Pre-Mounted 90 Degree Interface
  - Four C-Threaded Mounting Holes
  - Several Beamsplitting Options Available
  - Additional C-Mounted [Beamsplitters](#), [Filters](#), and [Mirrors](#) Available
- TECHSPEC® C-Mounted Plate Beamsplitters are designed to simplify system integration. These mounted beamsplitters include a TECHSPEC® Plate Beamsplitter pre-mounted in an Aluminum cube designed to interface with C-Mount (1" x 32 TPI) systems. Each cube is configured with four C-threaded holes, one on each face, and a ¼-20 tapped hole on the base for post mounting. TECHSPEC® C-Mounted Plate Beamsplitters are available in 30R/70T, 50R/50T, and 70R/30R options for either the visible or near infrared spectrum.

The C-Mounted Visible Plate Beamsplitters are designed for the 400 - 700nm wavelength range and the C-Mounted NIR Plate Beamsplitters are designed for the 700 - 1100nm wavelength range.

**Note:** These products cannot be disassembled. For mounting an alternative beamsplitter in a C-Mount Cube, use either [#56-264](#) or [#56-265](#).

## Technical Information



