

18mm Max. Aperture, Iris Diaphragm



Stock **#36-623** 3-5 DAYS

-

1

+

\$82.65

ADD TO CART

Qty 1-4

\$82.65

Qty 5+

\$73.08

Volume Pricing

[Request Quote](#)

Get Product Downloads

Type:
Unmounted

Minimum Aperture (mm):
1.5

Maximum Aperture (mm):
18.0

Outer Diameter (mm):
31.0

Construction: Aluminum Housing, Blue Tempered Spring Steel Leaves
Lever Diameter (mm): 5.00
Lever Length (mm): 10.0
Number of Leaves: 11
Thickness (mm): 6.50

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant

