

3.25" x 4.00", 6.0" FL, Cylinder Fresnel Lens



Cylinder Fresnel Lenses

Stock **#46-114** 6 In Stock

-

1

+

S\$98⁷⁰

ADD TO CART

Volume Pricing	
Qty 1-10	S\$98.70 each
Qty 11-49	S\$88.20 each
Need More?	Request Quote

Product Downloads

General

Fresnel Lens

Type:

Physical & Mechanical Properties

0.06

Center Thickness CT (inches):

±0.05

Dimensional Tolerance (inches):

Dimensions (inches):

3.25 x 4.0	
82.55 x 101.6	Dimensions (mm):
3.0 x 4.0	Effective Size (inches):
±0.020	Thickness Tolerance (inches):

Optical Properties	
152.40	Effective Focal Length EFL (mm):
Acrylic	Substrate: ☐
Uncoated	Coating:
400 - 1100	Wavelength Range (nm):
6.00	Effective Focal Length EFL (inches):
65.00	Groove Density (grooves/inch):
1.49	Index of Refraction (n _d):
85 (Typical)	Transmission (%):

Environmental & Durability Factors	
80 (Maximum)	Operating Temperature (°C):

Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 242:

Product Details

- Collapsed Version of a Standard Cylinder Lens
- Ideal for Focusing One Dimension
- Various Sizes Available

Technical Information

