

[See all 8 Products in Family](#)

35mm FL, Corning® Varioptic® C-C Series C-Mount Liquid Lens



Stock #91-615 **NEW** [CONTACT US](#)

⊖ 1 ⊕ **S\$2,093⁰⁰**

ADD TO CART

Volume Pricing

Qty 1+	S\$2,093.00 each
Need More?	Request Quote

Product Downloads

General

C-mount Lens

Type:

Optical Properties

35.00	Focal Length FL (mm):
200 - ∞	Working Distance (mm):
f/5.5 - f/22	Aperture (f/#):
VIS	Lens Wavelength Range:

Sensor

1.1"	Sensor Format:
2.74	Pixel Size (µm):

Threading & Mounting

C-Mount	Mount:
---------	---------------

Environmental & Durability Factors

50	Operating Temperature (°C):
45	Storage Temperature (°C):

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:

Product Details

- Electronically Controllable Focus
- Ideal For Machine Vision Applications
- Compatible With Up to 1.1", 20mpx Sensors
- C-Mount for Seamless Integration into Imaging Systems

Corning® Varioptic® C-C Series C-Mount Liquid Lens Evaluation Kits feature an electronically controllable liquid lens and integrated driver electronics in a compact, C-Mount design. With rapid switching times, no moving parts, and AR-Coatings for excellent transmission in the VIS and NIR, these lenses are an ideal solution for autofocus applications demanding clarity, durability, and speed. Designed for seamless integration into C-Mount machine vision and imaging systems, the lenses are compatible with sensors up to 1.1". Corning® Varioptic® C-C Series C-Mount Variable Focus Liquid Lenses' integrated electronics allow the lenses to be powered by a simple DC supply and controlled through RS-232, I²C, or SPI interfaces. Evaluation kits include Lenses, USB-M Universal, USB Cable, and Focuslab Software Control Software and Documentation Package.