

## 38mm Diameter Float Glass Window



Stock #02-184 **20+ In Stock**

- 1 + \$27<sup>65</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-5	\$27.65 each
Qty 6-49	\$25.20 each
Qty 50-99	\$23.80 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

#### General

Protective Window **Type:**  
Glass **Type of Window:**

#### Physical & Mechanical Properties

38.00 **Diameter (mm):**

1.50	<b>Thickness (mm):</b>
Fine Ground	<b>Edges:</b>
<b>Optical Properties</b>	
Uncoated	<b>Coating:</b>
Float Glass	<b>Substrate:</b> □
80-50	<b>Surface Quality:</b>
350 - 2000	<b>Wavelength Range (nm):</b>
4 - 6λ	<b>Surface Flatness (P-V):</b>
<b>Regulatory Compliance</b>	
<a href="#">Compliant</a>	<b>RoHS 2015:</b>
<a href="#">View</a>	<b>Certificate of Conformance:</b>
<a href="#">Compliant</a>	<b>Reach 247:</b>

### Product Details

- Transmits Visible and Near Infrared Wavelengths
- Available Uncoated or with an Anti-Reflection Coating
- Variety of Sizes Available

Float Glass Optical Windows are optical glass with polished faces that are relatively parallel and are typically used as a protective element between two environments. Float glass readily transmits visible and near-infrared wavelengths and can be used in a wide variety of applications. Float Glass Optical Windows are versatile products offered in circular and rectangular options. They are available uncoated or with BBAR (Broadband Anti-Reflective) 400-700nm coating.

### Compatible Mounts