

4-10mm FL, C-Mount, P-Iris, IR Cut Standard Lens



Image represents #22-825: Design will vary by stock number.



Stock **#22-818** 1 In Stock

-

1

+

S\$949^{.75}

ADD TO CART

Volume Pricing	
Qty 1+	S\$949.75 each
Need More?	Request Quote

Note: This item requires accessories for use | [Learn More](#)

Product Downloads

SPECIFICATIONS

General

Varifocal Lens

Type:

Physical & Mechanical Properties	
P-iris	Iris Option:
51.50	Length (mm):
Not Specified	Maximum Diameter (mm):
78	Weight (g):
Optical Properties	
112 - 44	Horizontal Field of View @ Max Sensor Format:
4-10	Focal Length Range (mm):
Not Specified	Working Distance (mm):
F/1.4 to closed	Aperture (f/#):
VS	Lens Wavelength Range:
Sensor	
1/1.7"	Maximum Sensor Format:
Threading & Mounting	
C-Mount	Mount:
Regulatory Compliance	
View	Certificate of Conformance:

PRODUCT DETAILS

- 4 - 10mm Focal Length Range for up to 135° Horizontal FOV
- True 4K, 12 Megapixel Resolution
- IR corrected for Day or Night

4K Wide Angle Lenses provide a wide range of fields of view for applications with long working distance requirements, allowing for excellent resolution up to 12 megapixels. Available with DC auto-iris, P-iris, and manual iris versions, these lenses are ideal for a wide range of applications including Intelligent Traffic (ITS), remote sensing, security, and robotics. The lenses are IR corrected for use with true Day/Night cameras, providing a bright image in both visible and IR illumination without manual adjustment. Lens mounting options include S-mount (M12), CS-mount, and C-mount with motorized and non-motorized versions available.