

# 4" Fiber Optic Diffuse Axial Illuminators



4" Fiber Optic Diffuse Axial Illuminators (#53-381)



Stock **#53-381** 3-5 DAYS

- 1 +

**S\$1,152.75**

ADD TO CART

Qty 1+

S\$1,152.75

Volume Pricing

[Request Quote](#)

**Note:** This item requires accessories for use | [Learn More](#)

Get Product Downloads

**Numerical Aperture NA:**  
0.55 nominal

**Fiber Diameter (µm):**  
50 (0.002" nominal)

**Construction:**  
Black Anodized Aluminum

|                                                          |
|----------------------------------------------------------|
| <b>Packing Fraction (%)</b> :<br>83% nominal             |
| <b>Transmission Loss</b> :<br>10% per ft. at 660nm       |
| <b>Type of Illumination</b> :<br>Fiber Optic Light Guide |
| <b>Geometry</b> :<br>Diffuse Axial                       |

Regulatory Compliance

|                                                             |
|-------------------------------------------------------------|
| <b>Reach 174</b> :<br><a href="#">Compliant</a>             |
| <b>RoHS</b> :<br>Not Compliant                              |
| <b>Certificate of Conformance</b> :<br><a href="#">View</a> |

---