

[See all 10 Products in Family](#)

TECHSPEC® 40mm - 65mm Length, T-Mount Fine Focus Tube



Stock #58-755 **2 In Stock**

⊖ 1 ⊕ S\$176⁰⁰

ADD TO CART

Volume Pricing

Qty 1-4	S\$176.40 each
Qty 5-9	S\$156.24 each
Qty 10-25	S\$144.34 each
Need More?	Request Quote

Product Downloads

General

Fine Focus Tube **Type:**
Extension Tube (Adjustable) **Function:**

Physical & Mechanical Properties

40.0 - 65.0 **Extension Length (mm):**

33.0 Clear Aperture CA (mm):

48.0 Outer Diameter (mm):

Threading & Mounting

T-Mount Thread Type:

M33 x 0.5 Barrel Thread:

Regulatory Compliance

Compliant RoHS 2015:

View Certificate of Conformance:

Compliant Reach 235:

Product Details

- Finely Threaded Internal Barrel for Fine Focus Adjustments
- Inner Diameter Baffle Thread for Stray Light Reduction
- Knurled Lip on Female End for Controlled Adjustments

TECHSPEC® C, S, and T-Mount Fine Thread Focus Tubes are used for making precision adjustments to optical element positions within a system. These tubes feature an outer barrel with male C, S, or T-Mount thread at the base end and a finely threaded interior barrel to allow for fine focusing. The secondary barrel has a female S, C, or T-Mount thread, knurled ring at the front end for easy adjustment, and a threaded interior for light baffle. Set screws can be used to fix the extension position. TECHSPEC C, S, and T-Mount Fine Thread Focus Tubes offer different extension length options to meet specific application demands.

Note: Compatible Allen wrenches for C, S, and T-Mount Fine Thread Focus Tubes ([#56-271](#), [#55-452](#), and [#58-637](#), respectively) sold separately.

Technical Information

