

40 lp/mm, 1" x 3", FS w/ Fluorescent, Ronchi



Stock #57-877 CLEARANCE 5 In Stock

S\$590⁰⁰

ADD TO CART

Volume Pricing

Qty 1-4	S\$590.80 each
Qty 5+	S\$561.82 each
Need More?	Request Quote

Product Downloads

Physical & Mechanical Properties

3.00	Length (inches):
12.7 x 25.4	Pattern Size (mm):
1.10	Thickness (mm):
1.00	Width (inches):

Optical Properties

Coating:
Vacuum Deposited Chrome
Fluorescent Peak Excitation @ 365 nm; Fluorescent
Peak Emission @ 550 nm

Frequency (lp/mm):
40.00

Substrate:
[Fused Silica](#) with Fluorescent Backing

Optical Density OD (Average):
3.00

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

Reach 240:
[Compliant](#)

Product Details

- Used for Evaluation of Resolution, Field Distortion, and Parfocal Stability
- Ideal for Reticle and Field Calibration Requirements
- Available on Float Glass, Fused Silica, Fused Silica with Fluorescent Backing, and [Opal](#).

Precision Ronchi Ruling Glass slides are excellent for evaluating resolution, field distortion, and parfocal stability, especially of microscopes. Many different Linepairs Per Millimeter (lp/mm) versions available.

;