

40 lp/mm 1" x 3", Opal Glass Ronchi Ruling Slide



Stock #59-547 **2 In Stock**

⊖ 1 ⊕ **\$450⁰⁰**

ADD TO CART

Volume Pricing	
Qty 1-4	\$450.80 each
Qty 5+	\$428.82 each
Need More?	Request Quote

Product Downloads

General

Pattern Location is Centered **Note:**

No **NIST Certification:**

Physical & Mechanical Properties

±0.100 **Dimensional Tolerance (inches):**

25.40 **Length (mm):**

12.7 x 25.4

Pattern Size (mm):

1.52 ±0.100

Thickness (mm):

76.20

Width (mm):

±0.001

Line Width Tolerance (µm):

Optical Properties

Vacuum Deposited Chrome

Coating:

40.00

Frequency (lp/mm):

Opal Glass

Substrate:

>3.0

Optical Density OD (Average):

40-20

Surface Quality:

Regulatory Compliance

[Compliant](#)

RoHS 2015:

[View](#)

Certificate of Conformance:

[Compliant](#)

Reach 235:

Product Details

Opal Glass material has been discontinued by the manufacturer and may be available in limited quantities. [Contact us](#) for more information.

- Chrome on Opal
- Test Resolution of Reflective Systems
- High Tolerance