

TECHSPEC[®] 40.0mm Dia. x 60.0mm FL, Uncoated, Plano-Convex Lens



Stock **#45-149** 3-5 DAYS

[Other Coating Options](#)



1



S\$61.63

ADD TO CART

Qty 1-9

S\$61.63

Qty 10+

S\$55.46

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
40.00 +0.0/-0.025

Effective Focal Length EFL (mm):
60.00 @ 587.6nm

Back Focal Length BFL (mm): 53.90
Coating: Uncoated
Substrate:  N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 9.31 ±0.10
Edge Thickness ET (mm): 2.00
Radius R₁ (mm): 31.03
Clear Aperture CA (mm): 39
f#: 1.5
Numerical Aperture NA: 0.33
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 350 - 2200

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant
