


TECHSPEC[®] 40mm 50R/50T Cube Beamsplitter



Stock #32-506 3-5 DAYS

-

1

+

S\$607.55

ADD TO CART

Qty 1-5

S\$607.55

Qty 6+

S\$485.75

Volume Pricing

[Request Quote](#)

Get Product Downloads



Beam Deviation (arcmin):
±3

Bevel:
Protective bevel as needed

Coating:
λ/4 MgF₂ @ 550nm on Faces
Multilayer Dielectric on Hypotenuse

Construction: Cube
Dimensions (mm): 40.0 x 40.0 x 40.0 ±0.10
Reflection/Transmission Ratio (R/T): 50/50
Reflection/Transmission Tolerance (%): ±5
Substrate: ☐ N-BK7
Surface Flatness (P-V): λ/4
Surface Quality: 60-40
Type: Standard Beamsplitter
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS 2015: Compliant
Reach 223: Compliant
Certificate of Conformance: View