

**TECHSPEC®** 40mm, 60mm Radius, English Goniometer



40mm, 60mm Radius, English Goniometer

Stock **#66-526** 3-5 DAYS

⊖ 1 ⊕ **S\$713.40**

ADD TO CART

Qty 1-2

S\$713.40

Qty 3+

S\$622.63

Volume Pricing

[Request Quote](#)

Get Product Downloads

Type of Movement:  
Goniometer

Type of Drive:  
Lead Screw

Type:  
English

Stage Size (mm):

|                                                          |
|----------------------------------------------------------|
| 40 x40                                                   |
| <b>Travel (°):</b><br>±10                                |
| <b>Construction:</b><br>Brass Stage                      |
| <b>Leadscrew Pitch (mm):</b><br>0.5                      |
| <b>Load Capacity (kg):</b><br>3                          |
| <b>Mounting Threads:</b><br>(1) ¼-20, (4) 6-32, (8) 2-56 |
| <b>Radius R (mm):</b><br>60                              |
| <b>Resolution (arcmin):</b><br>5                         |
| <b>Stage Size (inches):</b><br>1.57 x 1.57               |
| <b>Weight (kg):</b><br>0.3                               |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 233:</b><br><a href="#">Compliant</a>             |