

40X DIN Semi-Plan, Finite Intl Standard Objective



Stock #33-471 3-5 DAYS

- 1 + **S\$229.10**

ADD TO CART

Qty 1+

S\$229.10

Volume Pricing

[Request Quote](#)

Get Product Downloads

Design Wavelength DWL (nm):
546

Field of View (mm):
0.5

Focal Length FL (mm):
4.00

Length excluding Threads (mm):
44.40

Magnification:
40X

Maximum Diameter (mm): 25
Numerical Aperture NA: 0.65
Mounting Threads: RMS / 20.32mm x 36 TPI
Compatible Tube Lens Focal Length (mm): Focal Length: 160mm
Type: Semi-Plan
Depth of Field (µm): 1.89
Field of View, 18 Diameter Field Eyepiece (mm): 0.45
Operating Temperature (°C): +10 to +40
Operating Humidity: Max 85% at 35°C with no condensation
Working Distance (mm): 0.65
Weight (g): 83.4
Wavelength Range (nm): 400 - 700
Style: Finite Conjugate
Field Number (mm): 20
Parfocal Length (mm): 45.05
Immersion Liquid: N/A

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View