

40X Objective, Nikon CFI Super Fluor

See More by [Nikon](#)



Stock **#88-377** [CONTACT US](#)

- 1 + **S\$5,646.30**

ADD TO CART

Qty 1+
S\$5,646.30

Volume Pricing
Request Quote

Get Product Downloads

Compatible Cover Glass Thickness (mm):
0.11 - 0.23

Field of View (mm):
0.55

Horizontal Field of View, 1/2" Sensor:
0.16mm

Horizontal Field of View, 2/3" Sensor:
0.22mm

Model Number:
MRF00400

Length (mm): 59.60
Length excluding Threads (mm): 59.60
Magnification: 40X
Maximum Diameter (mm): 34.5
Maximum Sensor Format: 2/3"
Numerical Aperture NA: 0.90
Mounting Threads: M25 x 0.75
Compatible Tube Lens Focal Length (mm): Focal Length: 200mm
Type: Microscope Objective
Working Distance (mm): 0.3
Weight (g): 216
Style: Infinity Corrected
Manufacturer: Nikon
Field Number (mm): 22
Parfocal Length (mm): 59.9
Immersion Liquid: N/A

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View