

45° 5mm Output Dia., Molded Compound Parabolic Concentrator



Molded Compound Parabolic Concentrators (CPCs)



Stock #17-710 3-5 DAYS

− 1 +

S\$243.60

ADD TO CART

Qty 1-5
S\$243.60
Qty 6+
S\$195.03
Volume Pricing
Request Quote

Get Product Downloads

Substrate: ☐ B270

Coating: Uncoated

Type:

Specialty Lens
Wavelength Range (nm): 350 - 2500
Input Diameter (mm): 10.70
Length (mm): 18.04 ±0.10
Outer Diameter (mm): 17.00 ±0.20
Output Diameter (mm): 5.00
Surface Quality: 80-50
Acceptance Angle (°): 45

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View