

4.5mm Diameter Float Glass Window



Stock **#30-648** **20+ In Stock**

- 1 + S\$24^{.15}

ADD TO CART

| Volume Pricing | |
|----------------|-------------------------------|
| Qty 1-5 | S\$24.15 each |
| Qty 6-49 | S\$22.40 each |
| Qty 50-99 | S\$21.00 each |
| Need More? | Request Quote |

Product Downloads

General

Protective Window **Type:**
Glass **Type of Window:**

Physical & Mechanical Properties

4.50 **Diameter (mm):**

| | |
|------------------------------|--|
| 1.00 | Thickness (mm): |
| Fine Ground | Edges: |
| Optical Properties | |
| Uncoated | Coating: |
| Float Glass | Substrate: <input type="checkbox"/> |
| 80-50 | Surface Quality: |
| 350 - 2000 | Wavelength Range (nm): |
| 4 - 6λ | Surface Flatness (P-V): |
| Regulatory Compliance | |
| Compliant | RoHS 2015: |
| View | Certificate of Conformance: |
| Compliant | Reach 247: |

Product Details

- Transmits Visible and Near Infrared Wavelengths
- Available Uncoated or with an Anti-Reflection Coating
- Variety of Sizes Available

Float Glass Optical Windows are optical glass with polished faces that are relatively parallel and are typically used as a protective element between two environments. Float glass readily transmits visible and near-infrared wavelengths and can be used in a wide variety of applications. Float Glass Optical Windows are versatile products offered in circular and rectangular options. They are available uncoated or with BBAR (Broadband Anti-Reflective) 400-700nm coating.

Compatible Mounts