

**TECHSPEC® 45mm Focal Length f/4, Relay Lens**



TECHSPEC RelayLenses

Stock **#45-760** 3-5 DAYS

- 1 + **S\$565.50**

ADD TO CART

Qty 1-5

S\$565.50

Qty 6+

S\$452.40

Volume Pricing

[Request Quote](#)

Get Product Downloads

Diameter (mm):  
25.00

Effective Focal Length EFL (mm):  
45.00

Horizontal Field of View, 2/3" Sensor:  
11.00mm

Number of Lenses:

|                                                     |
|-----------------------------------------------------|
| 10                                                  |
| <b>Aperture (f/#):</b><br>f/4                       |
| <b>Length (mm):</b><br>72.70                        |
| <b>Maximum Sensor Format:</b><br>2/3"               |
| <b>Object to Image Track Length (mm):</b><br>127.60 |
| <b>Type:</b><br>Relay Lens                          |
| <b>Object Distance (mm):</b><br>24.50               |
| <b>Image Distance (mm):</b><br>30.50                |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Reach 209:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |

---