

[See all 46 Products in Family](#)

4" x 4" (50 lp/inch), Ronchi Ruling



Stock #56-618 [CONTACT US](#)

- 1 + \$677^{.60}

ADD TO CART

Volume Pricing	
Qty 1-4	\$677.60 each
Qty 5+	\$644.70 each
Need More?	Request Quote

Product Downloads

General

English **Type:**

Physical & Mechanical Properties

Dimensional Tolerance (inches):
±0.02

Dimensions (inches):
4 x 4

Thickness (mm):
1.50

±60	Parallelism (arcmin):
± 0.02	Dimensional Tolerance (mm):
≤2	Line to Line Parallelism (arcsec):
±1	Parallelism of Pattern to Substrate (°):

Optical Properties

Vacuum Deposited Chrome, OD >3.0	Coating:
Float Glass	Substrate: □
3.00	Optical Density OD (Average):
20-10	Surface Quality:
50.00	Frequency (lp/inch):
1λ	Surface Flatness (P-V):

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 240:

Product Details

- Chrome on Glass
- High Tolerance
- Superior to Etched and Filled Rulings
- Lines Parallel to Edge
- English and Metric Versions Available

High Precision Ronchi Rulings are excellent for evaluating resolution, field distortion, and parfocal stability. The glass targets are coated with vacuum-deposited chrome and have a float glass substrate. English and Metric version are available with various Linepairs Per Inch (LPI) and Linepairs Per Millimeter (lp/mm) measurements. High Precision Ronchi Rulings are offered in 0.5", 1", 2", and 4" squares.