

TECHSPEC[®] 50 x 50mm Enhanced Aluminum, λ/4 Mirror



Stock #45-336 [CONTACT US](#)

-

1

+

S\$152.25

ADD TO CART

Qty 1-5

S\$152.25

Qty 6+

S\$121.80

Volume Pricing

[Request Quote](#)

Get Product Downloads



Surface Flatness (P-V):
λ/4

Substrate: 
[BOROFLOAT[®]](#)

Back Surface:
Commercial Polish

Surface Quality:

60-40
Dimensions (mm): 50.0 x 50.0
Dimensional Tolerance (mm): ±0.25
Coating Specification: R _{avg} >95% @450 - 650nm
Coating: Enhanced Aluminum (450-650nm)
Coating Type: Metal
Bevel: Protective bevel as needed
Clear Aperture (%): 85
Edges: Fine Ground
Thickness (mm): 10.00 ±0.25
Type: Flat Mirror
Wavelength Range (µm): 0.45 - 0.65
Wavelength Range (nm): 450 - 650
Length (mm): 50.00
Width (mm): 50.00
Damage Threshold, Reference:  0.2 J/cm ² @532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant