

50 x 50mm Left-Handed Circular Polarizing Film (CP42HE)



Stock **#88-085** CLEARANCE 3-5 DAYS

- 1 +

S\$29.93

ADD TO CART

Qty 1+
S\$29.93

Volume Pricing
Request Quote

Get Product Downloads

Substrate: [Polymer Film CP42HE](#)

Length (mm):
50.00

Operating Temperature (°C):
-40 to +80

Dimensions (mm):
50.0 x 50.0

Thickness (mm):
0.27 ±0.04

Transmission (%) : 42.00
Type : Left-Handed Circular Polarizer
Dimensional Tolerance (mm) : +0.0/-0.5
Construction : Polarizing Film
Wavelength Range (nm) : 400 - 700
Polarization Efficiency (%) : >99.90
Heat Resistance (°C x Hours) : 80 x 500
Width (mm) : 50.00
#Sorting : 16.00

Regulatory Compliance

RoHS 2015 : Compliant
Certificate of Conformance : View
Reach 235 : Contains SVHC(s)