


TECHSPEC® 50 x 50mm Protected Silver, λ/20 Mirror



Stock #34-399

CONTACT US

-

1

+

S\$442.25

ADD TO CART

Qty 1-5
S\$442.25
Qty 6+
S\$353.80
Volume Pricing
Request Quote

Get Product Downloads



Surface Flatness (P-V):

λ/20 (flatness pre-coating)

Substrate:

[Fused Silica](#) (Corning 7980)

Back Surface:

Commercial Polish

Surface Quality:

20-10
Dimensions (mm): 50.0 x 50.0 +0.00/-0.20
Coating Specification: R _{avg} >98% @ 450 - 2000nm R _{avg} >98% @ 2000 - 10,000nm
Coating: Protected Silver (450-10000nm)
Coating Type: Metal
Clear Aperture (%): 90.00
Edges: Ground, protective bevel as needed
Parallelism (arcsec): 30.00
Thickness (mm): 5.00
Type: Flat Mirror
Wavelength Range (nm): 450 - 10000
Length (mm): 50.00
Width (mm): 50.00

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant