

50.8mm Clear Aperture 40R/40T, Pellicle Beamsplitter



Pellicle Beamsplitters

Stock **#39-483** 3-5 DAYS

- 1 + **S\$421.95**

ADD TO CART

Qty 1-10
S\$421.95
Qty 11+
S\$358.73
Volume Pricing
Request Quote

Get Product Downloads



Clear Aperture CA (mm):
50.8

Coating:
Metal/Dielectric

Coating Specification:
40/40 @ 400 - 700nm

Construction: Pellicle
Diameter (mm): 63.50
Housing: Black Anodized Aluminum
Index of Refraction n_d: 1.5
Mount Thickness (mm): 6.35
Reflection/Transmission Ratio (R/T): 40/40 $\pm$ 5%
Substrate:  Nitrocellulose
Surface Quality: 40-20
Type: Pellicle Beamsplitter
Wavelength Range (nm): 400 - 700
Mounting Threads: 2-56
Thickness (μm): 2 +0.3/-0.0

Regulatory Compliance

RoHS 2015: Compliant
REACH 201: Compliant
Certificate of Conformance: View