

TECHSPEC® 50.8mm Dia. x 75mm FL, Uncoated, ZnSe Plano-Convex Lens

See More by [Coherent®](#)



TECHSPEC Zinc Selenide (ZnSe) Plano-Convex (PCX) Lenses

Stock **#39-538** 3-5 DAYS

[Other Coating Options](#)

⊖ 1 ⊕

S\$1,499.30

ADD TO CART

Qty 1-10
S\$1,499.30
Qty 11+
S\$1,349.37
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
50.80 +0.00/-0.10

Effective Focal Length EFL (mm):
75.00 @ 10.6µm

Back Focal Length BFL (mm): 72.71
Coating: Uncoated
Substrate:  Coherent® Infrared ZnSe
Surface Quality: 40-20
Power (P-V) @ 632.8nm: λ
Power (P-V) @ 10.6μm: $\lambda/10$
Irregularity (P-V) @ 10.6μm: $\lambda/20$
Centering, ETD (μm): ≤12.7
Center Thickness CT (mm): 5.50 ±0.10
Edge Thickness ET (mm): 2.39
Radius R₁ (mm): 105.20
Clear Aperture CA (mm): 45.72
f/#: 1.48
Numerical Aperture NA: 0.34
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 600 - 18000
Bulk Absorption Coefficient (cm⁻¹): <0.0005 @ 10.6μm
Surface Roughness (Angstroms): <50 RMS

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View