

TECHSPEC® 50mm Dia. x 150mm FL, VIS-NIR, Inked, Double-Convex Lens



Stock #45-907-INK 10-15 DAYS

-

1

+

S\$119.63

ADD TO CART

Qty 1-9

S\$119.63

Qty 10+

S\$107.66

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
50.00

Back Focal Length BFL (mm):
147.00

Effective Focal Length EFL (mm): 150.00
Coating: VIS-NIR (400-1000nm)
Coating Specification: R _{abs} ≤0.25% @ 880nm R _{avg} ≤1.25% @ 400 - 870 nm R _{avg} ≤1.25% @ 890 - 1000nm
Substrate: 
Surface Quality: 40-20
Centering (arcmin): <1
Bevel: Protective bevel as needed
Center Thickness CT (mm): 9.00
Center Thickness Tolerance (mm): ±0.10
Edge Thickness ET (mm): 4.90
Radius R₁=R₂ (mm): 153.49
Clear Aperture CA (mm): 49.00
f/#: 3.00
Focal Length Tolerance (%): ±1
Numerical Aperture NA: 0.17
Type: Double-Convex Lens
Wavelength Range (nm): 400 - 1000

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View