

TECHSPEC® 50mm Dia. x 75mm FL, 3-5µm Coated Germanium Meniscus Lens



Stock **#87-965** 3-5 DAYS

⊖ 1 ⊕

S\$1,586.30

ADD TO CART

Qty 1-5
S\$1,586.30
Qty 6+
S\$1,269.04
Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm):
50.00 +0.0/-0.1

Effective Focal Length EFL (mm):
75.00

Substrate: ☐
Germanium (Ge)

f/#:
1.5

Numerical Aperture NA: 0.33
Coating: BBAR (3000-5000nm)
Type: Meniscus Lens
Wavelength Range (nm): 3000 - 5000
Back Focal Length BFL (mm): 71.56
Center Thickness CT (mm): 5.00
Center Thickness Tolerance (mm): ±0.10
Centering (arcmin): <3
Clear Aperture (%): 90.00
Coating Specification: R _{avg} <3.0% @ 3 - 5µm
Edge Thickness ET (mm): 3.5
Focal Length Specification Wavelength (µm): 10.6
Radius R₁ (mm): 81.89
Radius R₂ (mm): 122.77
Surface Quality: 60-40
Wavelength Range (µm): 3 - 5

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant